

# TECHNICAL DATA SHEET

**Part No.** 211-60039  
**Article No.** 211-60039  
**Type** H3P



HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Material</b>              | Polyamide 6.6 (PA66)             |
| <b>Operating Temperature</b> | -40°F to +185°F (-40°C to +85°C) |
| <b>Flammability</b>          | UL 94 V-2                        |
| <b>UV Resistant</b>          | No                               |
| <b>Use Conditions</b>        | For Indoor Use Only              |
| <b>Color</b>                 | Natural (NA)                     |
| <b>Pkg. Qty.</b>             | 1000                             |
| <b>Carton Qty.</b>           | 8000                             |
| <b>Customs Number</b>        | 3926909988                       |

|                                          |         |
|------------------------------------------|---------|
| <b>Max. Bundle Diameter (imperial)</b>   | 0.26 "  |
| <b>Max. Bundle Diameter (metric)</b>     | 6.5 mm  |
| <b>Mounting Hole Centers (imperial)</b>  | 0.39 "  |
| <b>Mounting Hole Centers (metric)</b>    | 10.0 mm |
| <b>Mounting Hole Diameter (imperial)</b> | 0.17 "  |
| <b>Mounting Hole Diameter (metric)</b>   | 4.2 mm  |
| <b>Width (imperial)</b>                  | 0.39 "  |
| <b>Width (metric)</b>                    | 10.0 mm |

RoHS ✓

EN 45545-2