

# TECHNICAL DATA SHEET

**Part No.** 211-60059  
**Article No.** 211-60059  
**Type** H5P



HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Flammability</b>	UL 94 V-2
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Natural (NA)
<b>Pkg. Qty.</b>	1000
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	3926909988

<b>Max. Bundle Diameter (imperial)</b>	0.37 "
<b>Max. Bundle Diameter (metric)</b>	9.5 mm
<b>Mounting Hole Centers (imperial)</b>	0.43 "
<b>Mounting Hole Centers (metric)</b>	11.0 mm
<b>Mounting Hole Diameter (imperial)</b>	0.17 "
<b>Mounting Hole Diameter (metric)</b>	4.2 mm
<b>Width (imperial)</b>	0.39 "
<b>Width (metric)</b>	10.0 mm

RoHS 

EN 45545-2