

TECHNICAL DATA SHEET

Part No. TSRI-JBD2
Article No. 250-20002
Type TSR-JBD2



Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. All junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.

Description	Dual Gang Junction Box
Height (imperial)	2.77 "
Height (metric)	70.36 mm
Length (imperial)	4.94 "
Length (metric)	125.48 mm
Width (imperial)	5.02 "
Width (metric)	127.51 mm

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Ivory (IV)
Pkg. Qty.	1
Carton Qty.	25
Customs Number	3925900000

