

TECHNICAL DATA SHEET

Part No. FHD
Article No. 251-21409
Type G51ND



HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Material	Polyamide 6 (PA6)
Operating Temperature	-76°F to +203°F (-60°C to +95°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
US MILSPEC	MS21266-4N
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	82 ft
Carton Qty.	12
Customs Number	3926909988

Height (imperial)	0.244 "
Height (metric)	6.2 mm
Height 2 (imperial)	0.169 "
Height 2 (metric)	4.3 mm
Max. Panel Thickness (imperial)	0.19 "
Max. Panel Thickness (metric)	4.8 mm
Min. Panel Thickness (imperial)	0.13 "
Min. Panel Thickness (metric)	3.3 mm
Width (imperial)	0.331 "
Width (metric)	8.4 mm
Width 2 (imperial)	0.201 "
Width 2 (metric)	5.1 mm

HF ✓

RoHS ✓

NASM