

# TECHNICAL DATA SHEET

**Part No.** FHG  
**Article No.** 251-21709  
**Type** G51NG



HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Material</b>              | Polyamide 6 (PA6)                |
| <b>Operating Temperature</b> | -76°F to +203°F (-60°C to +95°C) |
| <b>Flammability</b>          | UL 94 HB                         |
| <b>Halogen Free</b>          | Yes                              |
| <b>UV Resistant</b>          | No                               |
| <b>US MILSPEC</b>            | MS21266-7N                       |
| <b>Use Conditions</b>        | For Indoor Use Only              |
| <b>Color</b>                 | Natural (NA)                     |
| <b>Pkg. Qty.</b>             | 82 ft                            |
| <b>Carton Qty.</b>           | 1                                |
| <b>Customs Number</b>        | 3926909988                       |

|                                        |         |
|----------------------------------------|---------|
| <b>Height (imperial)</b>               | 0.268 " |
| <b>Height (metric)</b>                 | 6.8 mm  |
| <b>Height 2 (imperial)</b>             | 0.189 " |
| <b>Height 2 (metric)</b>               | 4.8 mm  |
| <b>Max. Panel Thickness (imperial)</b> | 0.38 "  |
| <b>Max. Panel Thickness (metric)</b>   | 9.7 mm  |
| <b>Min. Panel Thickness (imperial)</b> | 0.32 "  |
| <b>Min. Panel Thickness (metric)</b>   | 8.1 mm  |
| <b>Width (imperial)</b>                | 0.52 "  |
| <b>Width (metric)</b>                  | 13.2 mm |
| <b>Width 2 (imperial)</b>              | 0.398 " |
| <b>Width 2 (metric)</b>                | 10.1 mm |

HF ✓

RoHS ✓

**NASM**