

TECHNICAL DATA SHEET

Part No. 251-30309
Article No. 251-30309
Type G51TC



HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Material	Polytetrafluoroethylene (PTFE)
Operating Temperature	-76°F to +500°F (-60°C to +260°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
US MILSPEC	MS21266-3T
Use Conditions	For Indoor and Outdoor Use
Color	Natural (NA)
Pkg. Qty.	9.7 ft
Carton Qty.	100
Customs Number	3926909988

Height (imperial)	0.169 "
Height (metric)	4.3 mm
Height 2 (imperial)	0.106 "
Height 2 (metric)	2.7 mm
Max. Panel Thickness (imperial)	0.13 "
Max. Panel Thickness (metric)	3.3 mm
Min. Panel Thickness (imperial)	0.08 "
Min. Panel Thickness (metric)	2.1 mm
Width (imperial)	0.224 "
Width (metric)	5.7 mm
Width 2 (imperial)	0.138 "
Width 2 (metric)	3.5 mm

RoHS ✓