

TECHNICAL DATA SHEET

Part No. 300-30957
Article No. 300-30957
Type HIS-PACK-9.5/4.7



HIS-PACK Heat Shrink is a general-purpose, thin-wall Polyolefin tubing that provides electrical insulation and protection against corrosion and mechanical abrasion. HIS-PACKs are available in multiple colors and ten sizes ranging from 1/16" (1.2mm) to 1" (25.4mm). Tubing is conveniently stored in a handy dispenser box with hang tag and is RoHS approved.

Material	Polyolefin, cross-linked (PO-X)
Shrink Ratio	2:1
Longitudinal Change After Shrinkage	+/-5%
Min. Shrink Temperature	+212 °F (+100 °C)
Operating Temperature	-67°F to +257°F (-55°C to +125°C)
Dielectric Strength	20 kV/mm
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Green-Yellow (GNYE)
Pkg. Qty.	16.4 ft
Carton Qty.	3
Customs Number	3926909988

Dielectric Strength	20 kV/mm
Length (imperial)	16.4 ft
Length (metric)	5.0 m
Max. Bundle Diameter (imperial)	0.185 "
Max. Bundle Diameter (metric)	4.7 mm
Min. Bundle Diameter (imperial)	0 "
Recovered Diameter (imperial)	0.17 "
Recovered Diameter (metric)	4.7 mm
Shrink Ratio	2:1
Supplied Diameter (imperial)	0.37 "
Supplied Diameter (metric)	9.5 mm
Tensile Strength	17 MPa
Wall Thickness (imperial)	.023 "
Wall Thickness (metric)	0.60 mm

RoHS

