

TECHNICAL DATA SHEET

Part No. 318-60013
Article No. 318-60013
Type TAN32-19/6



Material	Polyolefin, cross-linked (PO-X)
Adhesive	EVA hot melt adhesive
Shrink Ratio	3:1
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature	+230 °F (+110 °C)
Operating Temperature	-67°F to +257°F (-55°C to +125°C)
Dielectric Strength	24 kV/mm
Flammability	UL 224 VW-1
Halogen Free	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	164 ft
Carton Qty.	3
Customs Number	3926909988

Adhesive	EVA hot melt adhesive
Dielectric Strength	24 kV/mm
Length (imperial)	1968 "
Length (metric)	50000 mm
Recovered Diameter (imperial)	0.236 "
Recovered Diameter (metric)	6.0 mm
Shrink Ratio	3:1
Supplied Diameter (imperial)	0.748 "
Supplied Diameter (metric)	19.0 mm
Tensile Strength	14 MPa
Wall Thickness (imperial)	.085 "
Wall Thickness (metric)	2.15 mm

RoHS ✓

