


TECHNICAL DATA SHEET

Part No. 553-50010
Article No. 553-50010
Type HST4.8-1.6WH



HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

Material	Polyolefin, cross-linked (PO-X)
Shrink Ratio	3:1
Min. Shrink Temperature	+194 °F (+90 °C)
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Dielectric Strength	19.7 kV/mm
Abrasion Resistance	Medium
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant	No
US MILSPEC	SAE-AMS-DTL-23053/5 Class 1 and 3, MIL-STD-202G Method 215K, SAE-AS81531
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	1000
Carton Qty.	12
Customs Number	3917320000

Center Slit	Unslit
Height (imperial)	0.312 "
Height (metric)	7.92 mm
Outside Diameter (imperial)	0.187 "
Outside Diameter (metric)	4.74 mm
Width (imperial)	1.9 "
Width (metric)	48.26 mm

RoHS ✓

SAE®