

TECHNICAL DATA SHEET

Part No. TTDTHOUT
Article No. 556-00144
Type TTDTHOUT



HellermannTyton thermal transfer ribbons are designed for use in HellermannTyton thermal transfer printers. Available on 1/2" and 1" cores, the ribbons are coated side out and available in two different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.

Material	Polyester (PET)
Operating Temperature	+40°F to +300°F (+4°C to +82°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1
Carton Qty.	48
Customs Number	3702390100

Description	Black Ribbon, 4.0" x 984', 1" Core, DTH Resin
Length (imperial)	984.0 ft
Length (metric)	300 m
Print Method	thermal transfer print
Recommended Material	DTH / Polyolefine
Reel Length (imperial)	984.3 ft
Reel Length (metric)	300 m
Width (imperial)	4.0 "
Width (metric)	101.6 mm

RoHS 