

TECHNICAL DATA SHEET

Part No. TT822OUT3
Article No. 556-00156
Type TT822OUT3



HellermannTyton thermal transfer ribbons are designed for use in HellermannTyton thermal transfer printers. Available on 1/2" and 1" cores, the ribbons are coated side out and available in two different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.

Material	Polyester Film (PET)
Operating Temperature	+40°F to +300°F (+4°C to +82°C)
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Orange (OG)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	3702440160

Description	Orange Ribbon, 4.33" x 984', 1" Core, Polyester Film
Length (imperial)	984.0 ft
Length (metric)	300 m
Print Method	thermal transfer print
Recommended Material	100/250/336/822/822C/795/799
Reel Length (imperial)	984.0 ft
Reel Length (metric)	300 m
Width (imperial)	4.33 "
Width (metric)	110.0 mm

RoHS ✓