

TECHNICAL DATA SHEET

Part No. 556-00460
Article No. 556-00460
Type TTM460



HellermannTyton's TTM460 Series thermal transfer printers are designed for medium- to high-volume users of thermal transfer labels and ShrinkTrak. Their user-friendly design features a streamlined menu for simple navigation, while the built-in caddy allows even the largest label rolls to fit inside. The optional cutter can cut through the thickest material. The TTM460's 600 dpi print head provides the highest quality printing available. These printers handle all sizes of HellermannTyton's ShrinkTrak markers and can print on even the smallest labels.

Material	Plastic (PL)
Operating Temperature	+40°F to +104°F (+4°C to +40°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	8443321050

Annual Label Volume	1 to 100,000 per day
Print Resolution DPI	600 dpi
Height (imperial)	12.28 "
Height (metric)	312 mm
Length (metric)	406.4 mm
Max. Label Height (imperial)	78.0 "
Max. Print Width	4 "
Maximum Print Width (metric)	101.6 mm
Printer Memory	64 MB RAM
Print Head Type	600 dpi
Print Method	thermal transfer print
Print Speed	7.87" (199.8 mm)/sec.
Width (metric)	240 mm

RoHS ✓