

TECHNICAL DATA SHEET

Part No. 556-04037
Article No. 556-04037
Type TT4030



HellermannTyton's TT4030 Series thermal transfer printers are designed for high-volume, industrial-grade printing of thermal transfer labels and ShrinkTrak. Their user-friendly design features an informative display for simple navigation and instructional videos. The built-in caddy allows even the largest label rolls to fit inside, and the cutter can cut through the thickest material. The TT4030's print head delivers excellent results. This printer handles all sizes of HellermannTyton's ShrinkTrak markers and can print on even the smallest labels. Use with HellermannTyton's TagPrint Pro label printing software.

Material	Plastic (PL)
Operating Temperature	+40°F to +104°F (+4°C to +40°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	8443321050

Annual Label Volume	1 to 200,000 per day
Print Resolution DPI	300 dpi
Height (imperial)	11.34 "
Height (metric)	288 mm
Length (metric)	381.0 mm
Max. Label Height (imperial)	78.74 "
Max. Print Width	4 "
Maximum Print Width (metric)	105.70 mm
Min. Label Height (imperial)	.16 "
Printer Memory	256 MB RAM
Print Head Type	300 dpi, flat type
Print Method	thermal transfer print
Print Speed	up to 11.8" (300 mm)/sec.
Width (metric)	252 mm

