

TECHNICAL DATA SHEET

Part No. 558-00337
Article No. 558-00337
Type HT2OE250



Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.

Width (imperial)	2.0 "
Width (metric)	50.8 mm



Material	Type 1500, Vinyl, UV-stabilized, glossy (1500)
Adhesive	Acrylic
Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Orange (OG)
Pkg. Qty.	250 ft
Carton Qty.	12
Customs Number	3919102055