

TECHNICAL DATA SHEET

Part No. 558-00412
Article No. 558-00412
Type HTIAR4X25



HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant safety, warning and arc-flash labels. They are available on continuous rolls of 125' or die-cut shapes. The rolls are available in four widths from 1" to 4" and can be cut to any length for custom sizes. TagPrint® Pro software enables full-color printing of text and images using templates or custom layouts and conveniently asks the user for the label length when creating a new design. Using HellermannTyton inkjet labels saves the time and cost of ordering custom identification products online, for on-demand convenience with no minimums or long lead times.

Labels per Column	1
Labels per Row	1
Liner Width (imperial)	4.0 "
Liner Width (metric)	101.6 mm
Pkg. Qty.	25 ft
Width (imperial)	4.0 "
Width (metric)	101.6 mm



Material	Paper (PAP)
Adhesive	Acrylic
Operating Temperature	-20°F to +250°F (-28°C to +121°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only