

TECHNICAL DATA SHEET

Part No. 558-00416
Article No. 558-00416
Type HT4WTP101125



HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant safety, warning and arc-flash labels. They are available on continuous rolls of 125' in 1" to 4" widths or die-cut shapes. TagPrint® Pro software contains many common pre-saved safety label designs for easy editing. Save time and money compared to buying online, and no minimums to worry about.

Length (imperial)	125 ft
Width (imperial)	4.0 "
Width (metric)	101.6 mm



Material	Polyester (PET)
Adhesive	Acrylic
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	125 ft
Carton Qty.	5
Customs Number	3919102055