

TECHNICAL DATA SHEET

Part No. 558-00702
Article No. 558-00702
Type HT4WT101RP100



HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant safety, warning and arc-flash labels. They are available on continuous rolls of 125' or die-cut shapes. The rolls are available in four widths from 1" to 4" and can be cut to any length for custom sizes. TagPrint® Pro software enables full-color printing of text and images using templates or custom layouts and conveniently asks the user for the label length when creating a new design. Using HellermannTyton inkjet labels saves the time and cost of ordering custom identification products online, for on-demand convenience with no minimums or long lead times.

Length (imperial)	100 ft
Width (imperial)	4.0 "
Width (metric)	101.6 mm



Material	Paper (PAP)
Adhesive	Acrylic
Operating Temperature	-20°F to +250°F (-28°C to +121°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	100 ft
Carton Qty.	5
Customs Number	4821904000