

TECHNICAL DATA SHEET

Part No. 558-10001
Article No. 558-10001
Type HT35X5IJWP



HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant labels of all types. Die-cut labels come with rounded corners, ready to print safety, warning and arc-flash labeling. TagPrint® Pro software allows full-color printing of text and images. Using HellermannTyton inkjet labels saves the time and cost of ordering custom signs online, providing on-demand convenience with no minimums or long lead times.

Material	Polyester (PET)
Adhesive	Acrylic
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	50
Carton Qty.	5
Customs Number	3919102055

Height (imperial)	5.0 "
Height (metric)	127.0 mm
Labels per Column	1
Labels per Row	1
Width (imperial)	3.5 "
Width (metric)	88.9 mm

