

TECHNICAL DATA SHEET

Part No. TAG15J-450
Article No. 593-15450
Type TAG15J



HellermannTyton offers a series of technologically advanced labels for use on standard inkjet printers. The labels come on 8.5" x 11" sheets and are printable using HellermannTyton's TagPrint Pro software. A wide range of materials and sizes is available for wire and component marking. When used with pigment based inks, HellermannTyton inkjet labels offer superior non-smear marks that are chemical and solvent resistant. Even colors can be printed when used on a color inkjet printer. Inkjet labels are available in polyester or paper.

Height (imperial)	1.0 "
Height (metric)	25.4 mm
Labels per Column	9
Labels per Row	13
Labels per Sheet	117
Width (imperial)	0.5 "
Width (metric)	12.7 mm

Material	Type 450, Polyethylene Terephthalate (450)
Adhesive	Acrylic
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	1
Customs Number	3919905060

RoHS ✓