

TECHNICAL DATA SHEET

Part No. TAG22J-994
Article No. 593-22994
Type TAG22J



HellermannTyton's ink jet self-laminating labels are smear resistant, allowing them to be handled immediately. The labels are made of a heat resistant 1mm polyester film with a strong acrylic based adhesive. The printable area is a special ink-receptive film that absorbs the ink as it is printed on an ink jet printer. Each sheet is smaller than the standard letter size (8.5" x 11".) Less waste results from the smaller sheet size because the user can print smaller quantities at one time. HellermannTyton's ink jet self laminating labels are also more convenient to store.

Height 2 (imperial)	1.43 "
Height 2 (metric)	36.32 mm
Labels per Column	4
Labels per Row	8
Labels per Sheet	32
Width (imperial)	1.0 "
Width (metric)	25.4 mm

RoHS ✓

Material	Type 994, Polyethylene Terephthalate (994)
Adhesive	Acrylic
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	1000
Carton Qty.	25
Customs Number	3919905060