

TECHNICAL DATA SHEET

Part No. TAG64J-994
Article No. 593-64994
Type TAG64J



Ink Jet labels are durable, ink jet printable markers for applications requiring clear, crisp legibility. The labels are supplied on sheets and are printable using HellermannTyton Tagprint Pro software and a standard ink jet printer. Specially designed adhesives and topcoats accept the ink allowing for easy color printing for specific applications that require colors.

Material	Type 994, Polyethylene Terephthalate (994)
Adhesive	Acrylic
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	1000
Carton Qty.	1
Customs Number	3919905060

Height 2 (imperial)	3.25 "
Height 2 (metric)	82.60 mm
Labels per Column	2
Labels per Row	7
Labels per Sheet	14
Width (imperial)	1.16 "
Width (metric)	29.6 mm

RoHS ✓