

TECHNICAL DATA SHEET

Part No. TAG79T1-795
Article No. 596-79795
Type TAG79T1



HellermannTyton's metalized polyester labels include a layer of metallic particles that give the appearance of being made of metal. Applications include asset tracking and product rating plates. The high operating temperature makes them suitable for use on electronic equipment. Great for replacing expensive metal stampings, engravings and even silk screened rating plates, the printed labels offer high quality imaging for text and graphics and can be permanently placed on a wide variety of flat surfaces.

Height (imperial)	2.0 "
Height (metric)	50.8 mm
Labels per Column	1
Labels per Row	1
Width (imperial)	4.0 "
Width (metric)	101.6 mm

Material	Type 795, Polyester (795)
Adhesive	Acrylic
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Silver (SR)
Pkg. Qty.	500
Carton Qty.	18
Customs Number	3919102055

