

TECHNICAL DATA SHEET

Part No. SM1BK75MT
Article No. 800-00004
Type SM1



EdgeGuard is used to cover panel edging to protect cables, prevent chafing and provide an attractive finish. The EdgeGuard is manufactured from a flexible PVC compound ensuring ease of use.

Material	Polyvinylchloride (PVC)
Operating Temperature	-85°F to +221°F (-65°C to +105°C)
Flammability	UL 94 HB
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	246 ft
Carton Qty.	6
Customs Number	3926909988

Height (imperial)	0.248 "
Height (metric)	6.3 mm
Height 2 (imperial)	0.193 "
Height 2 (metric)	4.9 mm
Max. Panel Thickness (imperial)	0.08 "
Max. Panel Thickness (metric)	2.0 mm
Min. Panel Thickness (imperial)	0.04 "
Min. Panel Thickness (metric)	1.0 mm
Width (imperial)	0.1969 "
Width (metric)	5.0 mm
Width 2 (imperial)	0.039 "
Width 2 (metric)	1.0 mm

RoHS

