

TECHNICAL DATA SHEET

Part No. ETCW660
Article No. 904-00010
Type ETCW66



Heavy duty vinyl tapes are ideal for outdoor applications. Tape provides fast, easy and economical cable splicing, terminating, wire insulating, and more. These conformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

Material	Flexible Polyvinyl Chloride (PVC)
Operating Temperature	-0.4°F to +194°F (-18°C to +90°C)
UV Resistant	No
US MILSPEC	MIL-1-24391-A
Use Conditions	For Indoor and Outdoor Use
Pkg. Qty.	10
Carton Qty.	200
Customs Number	3919102020

Length (imperial)	66.0 ft
Length (metric)	20.12 m
Pkg. Qty.	10
Thickness (imperial)	8.0 mil
Thickness (metric)	0.2 mm
Width (imperial)	0.75 "
Width (metric)	19.05 mm

