

TECHNICAL DATA SHEET

Part No. ETST6610
Article No. 904-00012
Type ETST66



PVC electrical tape provides fast and easy color coding, cable splicing, terminating, and wire insulating. These conformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

Material	Flexible Polyvinyl Chloride (PVC)
Operating Temperature	+20°F to 176°F (-7°C to +80°C)
UV Resistant	No
US MILSPEC	MIL-1-7798-A
Use Conditions	For Indoor Use Only
Pkg. Qty.	10
Carton Qty.	200
Customs Number	3919102020

Length (imperial)	66.0 ft
Length (metric)	20.12 m
Pkg. Qty.	10
Thickness (imperial)	7.0 mil
Thickness (metric)	0.18 mm
Width (imperial)	0.75 "
Width (metric)	19.05 mm

