

TECHNICAL DATA SHEET

Part No. 904-00921
Article No. 904-00921
Type CTPUV20



HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Material	Polyethylene, UV-resistant (PEUV)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	not flame retardant
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Pkg. Qty.	800 ft
Carton Qty.	800
Customs Number	3926909988

Length (imperial)	800.0 ft
Length (metric)	243.8 m
Nominal Diameter (imperial)	2 "
Nominal Diameter (metric)	50.8 mm
Outside Diameter (imperial)	2.388 "
Outside Diameter (metric)	60.66 mm
Pkg. Qty.	800 ft
Wall Thickness (imperial)	0.011 "
Wall Thickness (metric)	0.28 mm

HF✓

RoHS✓