


Common Mode Choke

TCK-076


Order Code	TCK-076
Inductance (each winding)	55 μ H $\pm 35\%$ (at 100 kHz / 20 mV)
Impedance (DCR)	8.5 m Ω max.
Rated Current	5.7 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-076




Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	11.5 max.
B	11.5 max.
C	8.8 max.
D	2.5 min.
E	7.62 ± 0.2
F	7.62 ± 0.2
G	$\varnothing 0.6 \pm 0.1$



All specifications valid at +25°C, unless otherwise stated.