


THIS IS ISSUED IN STRICT CONFIDENCE
THAT IT IS NOT USED AS A BASIS FOR
MANUFACTURE OR SALE AND THAT IT IS
NOT COPIED, REPRINTED OR
DISCLOSED TO A THIRD PARTY EITHER
WHOLLY OR IN PART WITHOUT THE
PRIOR WRITTEN CONSENT OF CAL TEST
ELECTRONICS, INC.

REVISONS

REV.	DESCRIPTION	DATE	APPROVED
A	CLASS A RELEASED	5/1/2023	B. HANSEN
B	ADDED ISOMETRIC VIEW.	6/5/2023	B. Hansen

NOTES:

1. INSULATED ALLIGATOR CLIP LEAD ASSEMBLY.
2. SPECIFICATIONS:
 - ALLIGATOR CLIPS:
 - CONDUCTOR: STEEL, NICKEL PLATED.
 - TIP INSULATORS: POLYPROPYLENE 3084H, FILE# E216959. (COLOR MATCHES WIRE).
 - SPRING: STAINLESS STEEL
 - BOOT: TPR (SANTOPRENE 201-55, FILE# E80017). COLOR MATCHES WIRE.
 - TEST LEAD: SILICONE JACKETED, DOUBLE-INSULATED, BARE COPPER, STRANDING 195x0.07mm, 0.75mm², 18AWG. (EASSAN, 3239 AWM, VW-1, UL 758, cULus). COLOR - SEE MODEL NUMBER.
 -
3. RATING:
 - IEC VOLTAGE: 1000 V CAT III / 600 V CAT IV.
 - CURRENT: 10 A MAX.
 - TEMPERATURE: 0°C TO +60°C MAX
4. RoHS 2 COMPLIANT.
5. AVAILABLE AS MODEL CT4485-L, BLACK AND RED PAIR OF CT4484-L-#.



THIRD ANGLE PROJECTION	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: XX = ±0.5 XX* = ±0.5* XXX = ±0.25 XXX* = ±0.125 DO NOT SCALE DRAWING	PROJECT NO. A645(a)	METRIC	Cal Test ELECTRONICS	22820 Savi Ranch Pkwy. Yorba Linda, CA 92887 USA
REFERENCE	APPROVALS	DATE	TITLE	LEAD, ALLIGATOR CLIPS, 1000V CAT III, SILICONE 18AWG	
	DRAWN WDH	5/1/2023			
	CHECKER				
	SEE NOTES				
	TREATMENT NONE	ENGR. B. HANSEN	5/1/2023	SIZE B	CAGE CODE 43F45
	FINISH SEE NOTES	DESIGN ACTIVITY		DWG. NO. CT4484	REV. B
			SCALE 1:1		SHEET 1 OF 1