

LOCTITE ECCOBOND UF 8830S

January 2017

PRODUCT DESCRIPTION

LOCTITE ECCOBOND UF 8830S provides the following product characteristics:

Technology	Epoxy
Appearance	Grey paste
Product Benefits	• High purity • High TG, low CTE • Improved toughness • Good flow with self filleting • Long staging time and worklife • 260°C reflow capability for Pb-free, low-k applications
Cure	Heat cure
Application	Underfill
Typical Package Application	Flip Chip BGA

LOCTITE ECCOBOND UF 8830S liquid epoxy underfill encapsulant is formulated for tight bump pitch and narrow gap in flip chip BGA applications. It is designed to improve crack/fracture resistance and deliver faster flow.

When fully cured, this material forms a rigid, low stress seal that dissipates stress in solder joints and extends thermal cycling performance.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield, °C, mPa·s (cP):

Spindle 51, Speed 5 rpm 22,120

Thixotropic Index 0.85

Specific Gravity @ 25°C 1.6

Work Life @ 25°C, (100% increase in viscosity), hours >24

Shelf Life @ -40°C, days 365

Flash Point - See SDS

TYPICAL CURING PERFORMANCE

Cure Schedule

30 minute ramp from 25°C to 150°C, hold 2hrs at 150°C

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, TMA, ppm/°C:

Below Tg 25

Above Tg 100

Glass Transition Temperature (Tg), °C:

By TMA 118

By DMA 126.5

Storage Modulus, DMA:

@ 25 °C

N/mm² 11,500
(psi) (1,667,934)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -40 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

(°C x 1.8) + 32 = °F

kV/mm x 25.4 = V/mil

mm / 25.4 = inches

N x 0.225 = lb

N/mm x 5.71 = lb/in

psi x 145 = N/mm²

MPa = N/mm²

N·m x 8.851 = lb·in

N·m x 0.738 = lb·ft

N·mm x 0.142 = oz·in

mPa·s = cP

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 0.2