

LOCTITE® SI 5620™

Known as Loctite® 5620™
January 2015

PRODUCT DESCRIPTION

LOCTITE® SI 5620™ provides the following product characteristics:

Technology	Silicone
Chemical Type	Alkoxy silicone
Appearance, Resin (Component A)	Clear to Colorless ^{LMS}
Appearance, Hardener (Component B)	Clear to Colorless ^{LMS}
Appearance (Mixture)	Clear liquid
Components	Two component - requires mixing
Cure	Room temperature vulcanizing (RTV)
Mix Ratio, by volume - Resin : Hardener	1 : 1
Application	• Potting • Protective from moisture, vibration, thermal shock and mechanical shock

LOCTITE® SI 5620™ is a two-component silicone that will cure at room temperature or at elevated temperatures. After mixing, the material cures quickly to form a clear, very flexible elastomer.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A:

Specific Gravity @ 22 °C	0.97
Viscosity, Brookfield, 25 °C, mPa·s (cP):	
Spindle 3, speed 20 rpm	200 to 450 ^{LMS}

Part B:

Specific Gravity @ 22 °C	0.97
Viscosity, Brookfield, 25 °C, mPa·s (cP):	
Spindle 3, speed 20 rpm	175 to 450 ^{LMS}

TYPICAL CURING PERFORMANCE

Gel Time

Gel time, 25 °C, minutes	7 to 15 ^{LMS}
--------------------------	------------------------

TYPICAL PROPERTIES OF CURED MATERIAL

After 15 minutes @ 150 °C

Physical Properties:

Shore Hardness, ISO 868, Durometer A	30 to 40 ^{LMS}
--------------------------------------	-------------------------

Cured for 72 hours @ 22 °C

Physical Properties:

Refractive Index	1.41
Coefficient of Thermal Conductivity ASTM F 433, W/(m·K)	0.16
Coefficient of Thermal Expansion, ISO 11359-2, K ⁻¹ :	
Pre Tg	244×10 ⁻⁶
Post Tg	315×10 ⁻⁶

Electrical Properties:

Dielectric Strength, IEC 60243-1, kV/mm	21.14
Dielectric Constant / Dissipation Factor, IEC 60250:	
1 KHz	2.46 / 0.03
100 KHz	2.52 / 0.0007
Volume Resistivity, IEC 60093, Ω·cm	3.0×10 ¹⁵

TYPICAL ENVIRONMENTAL RESISTANCE

Silicones provide excellent environmental resistance due to their unique chemical structure and the inherent properties of the materials.

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

Directions for use:

1. For high strength structural bonds, remove surface contaminants such as paint, oxide films, oils, dust, mold release agents and all other surface contaminants.
2. Use gloves to minimize skin contact. DO NOT use solvents for cleaning hands.
3. **Dual Cartridges:** To begin using a new cartridge, remove cartridge cap and dispense a small amount of adhesive, making sure both parts A&B are extruding. Attach nozzle and dispense approximately 25 to 50mm, before applying onto part to be bonded. Partially used cartridges can be stored with the mixing nozzle attached. To reuse, remove and discard old nozzle, attach the new nozzle, dispense approximately 25 to 50mm, before applying onto part to be bonded.
Bulk Containers: Normally material is dispensed through volumetric metered mixing equipment, attached to static mix nozzles.
4. Application to the substrates should be made as soon as possible. Larger quantities and/or higher temperatures will reduce the working time.
5. Keep assembled parts from moving during cure. The bond should be allowed to develop full strength before subjecting to any service load.
6. Excess material can be easily wiped away with non-polar solvents.

Loctite Material Specification^{LMS}

LMS dated October 27, 2008. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

(°C x 1.8) + 32 = °F
 kV/mm x 25.4 = V/mil
 mm / 25.4 = inches
 µm / 25.4 = mil
 N x 0.225 = lb
 N/mm x 5.71 = lb/in
 N/mm² x 145 = psi
 MPa x 145 = psi
 N·m x 8.851 = lb·in
 N·m x 0.738 = lb·ft
 N·mm x 0.142 = oz·in
 mPa·s = cP

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.2