




ASSEMBLY P/N	GROMMET I.D. / CABLE O.D. RANGE	CONTACT QTY
13382-10PG-440W	0.400 [10.2] / 0.320 - 0.400 [8.1 - 10.2]	(10) #16
13382-10PG-450W	0.500 [12.7] / 0.400 - 0.500 [10.2 - 12.7]	
13382-10PG-457W	0.570 [14.5] / 0.500 - 0.570 [12.7 - 14.5]	

NOTES:

1. ALL PARTS TO BE BULK PACKED.
2. RED SILICONE O-RING IS LUBRICATED AND INSTALLED INTO GROOVE OF CABLE CLAMP
3. CONTACTS ARE ASSEMBLED INTO CONNECTOR.
4. DIMENSIONS ARE REFERENCE ONLY EXCEPT THOSE WITH A TOLERANCE



SHOWN ASSEMBLED
FOR CUSTOMER REFERENCE ONLY



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	MA	06-11-24	RELEASED PER PDR 22008-6
	PNK	12-19-23	PRR# P-22008-6
REV.	INIT.	DATE	DESCRIPTION
			ORIG. DRAWN BY: PNK DATE: 12-19-23
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			
APPROVED BY:		TITLE: CABLE CONNECTOR ASS'Y (10) #16 PIN CONTACTS, SOLDER MAXI-CON-X	
SCALE	SIZE	SHEET	CUSTOMER: STANDARD PRODUCT
NTS	B	1 OF 1	
FILE:	DIRECTORY:	PART NUMBER:	REV
13382-10PG-4XXW	SLW	13382-10PG-4XXW	A

DIMENSIONS IN BRACKETS [] ARE METRIC

RoHS COMPLIANT

CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX