







CUSTOMER PRINT

PART NUMBER: 15180-XPG-4XX


- NOTES:
- 1. ALL PARTS TO BE BULK PACKED.
 - 2. RED SILICONE O-RING IS LUBRICATED AND INSTALLED INTO GROOVE OF CABLE CLAMP
 - 3. CONTACTS SUPPLIED UNASSEMBLED
 - 4. DIMENSIONS ARE REFERENCE ONLY EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	GROMMET SIZE
15180-XPG-440	GROMMET ID .400 [10.2] FOR CABLE OD .320 - .400 [8.1 - 10.2]
15180-XPG-450	GROMMET ID .500 [12.7] FOR CABLE OD .400 - .500 [10.2 - 12.7]
15180-XPG-457	GROMMET ID .570 [14.5] FOR CABLE OD .500 - .570 [12.7 - 14.5]





ASS'Y P/N	CONTACT QTY
15180-2PG-4XX	2
15180-3PG-4XX	3
15180-4PG-4XX	4
15180-7PG-4XX	7



DETAIL A



SHOWN ASSEMBLED
FOR CUSTOMER REFERENCE ONLY



CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

A	MA	07-17-24	RELEASED PER PDR 22008-7		
	PNK	12-19-23	PRR# P-22008-7		
REV.	INIT.	DATE	DESCRIPTION		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK		DATE: 12-19-23
			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			conxall 601 E. WILDWOOD VILLA PARK, IL 60181		
APPROVED BY:			TITLE: INLINE CONNECTOR ASS'Y (2-4,7) #12 PIN CONTACTS, CRIMP MAXI-CON-X		
SCALE NTS			CUSTOMER: STANDARD PRODUCT		
SIZE B			PART NUMBER: 15180-XPG-4XX		
SHEET 1 OF 1			REV A		
FILE: 15180-XPG-4XX			DIRECTORY: SLW		

DIMENSIONS IN BRACKETS [] ARE METRIC

RoHS COMPLIANT

➤ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX