









FRONT OF THE JACK



SCHEMATIC



PCB LAYOUT

COMPONENT SIDE

TOLERANCE: ±0.002 [±0.05]

NOTES:

1. MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, SILVER PLATED
2. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.
3. ALL DIMENSIONS ARE REFERENCED.
4. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
B	28775	10/13/25	PC	TJK
A	28481	03/03/22	PC	TJK

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]

- TWO PLACE DECIMALS ±0.02 [0.5]

- THREE PLACE DECIMALS ±0.005 [0.13]


DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON			SCALE 6:1		Switchcraft®				
DATE DRAWN	BY	CHKD	APVD						
10/27/21	TS	TS	TJK	10/27/21		3/1/22		SHEET 1 OF 2	
NAME 3.5MM JACK, 4 CONDUCTOR, SURFACE MOUNT, RoHS					PART No. 35RASMT5CHNTRX				REV B

SolidWorks CAD File


A: CARRIER SIZE

- 1. DETAIL SIZE REFERENCES: EIA-481
- 2. SPECIFICATIONS: 32 MM X 16 MM



B: REEL SIZE

- 1. QUANTITY: 500 PCS/REEL (B)
- 2. MATERIAL: THERMOPLASTIC



CUSTOMER DRAWING

SCALE NONE	Switchcraft®		
DATE DRAWN 3/1/22			
	SHEET 2 OF 2		
DRAWN BY TJK	PART No. 35RASMT5CHNTRX	REV B	