


ST-605
OVERMOLDED 5 PIN FEMALE TINI QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.




ST-605
FRONT MATING VIEW
BOTH ENDS

WIRING CHART STRAIGHT THRU WIRING		
ST-605	WIRE COLOR	ST-605
PIN 1	BLACK	PIN 1
PIN 2	WHITE	PIN 2
PIN 3	RED	PIN 3
PIN 4	GREEN	PIN 4
PIN 5	BROWN	PIN 5
SHELL	SHIELD/ DRAINWIRE	SHELL

ST-605
OVERMOLDED 5 PIN FEMALE TINI QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.



CUSTOMER DRAWING

NOTES:

1. THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.
					UNLESS OTHERWISE SPECIFIED
					1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]
B	28753	07/24/25	PC	TJK	SIZE
A	28310	08/25/20	PC	TJK	WIDTH
REV	ECO NUMBER	DATE	BY	APVD	MULT
					LBS/M
					TEMPER
					FINISH
					SPEC No.
					MATERIAL
					SPEC No.
					FIRST USED ON
					SCALE
					1.5:1
					DATE DRAWN
					BY
					CHKD
					APVD
					TJK
					7/28/20
					8/10/20
					SHEET 1 OF 1
					NAME
					CABLE ASSEMBLY, DOUBLE
					ENDED 5 PIN FEMALE TINI QG, RoHS
					PART No.
					605HJ_605X
					REV
					B

REVISIONS

DO NOT SCALE DRAWING