



DB25 PIN-OUT VIEW FOR DB25

DB25 AND XLR FEMALE WIRING CHART				
XLR (CHANNEL)	CABLE	PIN 2 (COLOR)	PIN 3 (RED)	PIN 1 (BLACK)
1	BROWN	24	12	25
2	RED	10	23	11
3	ORANGE	21	9	22
4	YELLOW	7	20	8
5	GREEN	18	6	19
6	BLUE	4	17	5
7	PURPLE	15	3	16
8	GRAY	1	14	2

NOTES:

1. BREAKOUT CABLE LENGTH: 18.00 +/- 0.75 INCHES. SEE TABLE FOR COLOR.

2. THIS PRODUCT COMES COILED AND PACKAGED IN BAG.

3. JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (2) AND #M3 THREAD (2) JACKSCREWS.

4. MATERIALS:

XLR FEMALE CONNECTOR:

HANDLE - ZINC ALLOY, NICKEL PLATED
HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED

INSULATOR - THERMOPLASTIC, GREEN

SOCKET CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED

H.S. TUBING - THERMOPLASTIC

DSUB - COPPER ALLOY, NICKEL PLATED WITH GOLD PINS

JACKSCREWS - STAINLESS STEEL

5. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<p>UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ± 0.02 - THREE PLACE DECIMALS ± 0.005</p>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
E	26891	11/29/11	TJK	TJK		SIZE				
D	26795	7-8-11	TO	TJK		WIDTH				
C	26637	10/11/10	RS	TJK		MULT				
B	25891	9/9/08	SRC	TJK		LBS/M				
A	25716	10/03/07	JGK	TJK		TEMPER				
REV	ECO NUMBER	DATE	BY	APVD		FINISH				
						SPEC No.				
						FIRST USED ON		SCALE 2:1		
						DATE DRAWN	BY	CHKD RS	APVD TJK	Switchcraft®
						9/12/06	JGK	11/8/10	11/9/10	
						NAME				
						DB25M TO 8 FEMALE XLR, RoHS				
						PART No.	DB25M_XLRF			REV E

REVISIONS

DO NOT SCALE DRAWING