


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-2-110/133_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 6 GHz	30 dB	1.03
6 GHz ... 11 GHz	28 dB	1.04
11 GHz ... 18 GHz	23 dB	1.15

Mechanical data

Weight	0.0022 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-2-110/133_N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84130715	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
84117816	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84130715	11_SMA-50-2-110/133_NE	Single
84117816	11_SMA-50-2-110/133_NP	Bulk 500 pcs

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y16 - 2 mm / 50 Ohm
	Y11 - 2 mm / 50 Ohm
Suitable cables	SUCOFORM_86
	MULTIFLEX_86
	SR_86_TP_M17

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544557	74_Z-0-0-58	Assembly tool
22544555	74_Z-0-0-54	Holders
22544553	74_Z-0-0-52	Positioning aids
23024588	74_Z-0-0-442	Soldering tool
22648904	74_Z-0-0-263	Gauges
22643028	74_Z-0-0-164	Trimming tool
23021266	74_Z-0-0-369	Locator
22658180	74_Z-0-0-335	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3485 / Date of publication: 04.11.2025 / uncontrolled copy