

COAXIAL CONNECTOR, UHF, other Ohm, Straight cable plug (male)
11_UHF-0-7-4/002_-

Properties

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz



Product configuration		
Interface type	Gender	Standard
UHF	plug	IEC 60169-12
Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	Nickel Plating
Electrical data		
Interface frequency		0.2 GHz
Mechanical data		
Weight		0.0232 kg
Mating cycles		500
Cable entry centre contact		soldered
Cable entry outer contact		others
Environmental data		
Operation temperature		-55 °C ... 165 °C

COAXIAL CONNECTOR, UHF, other Ohm, Straight cable plug (male)

11_UHF-0-7-4/002_-

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22542728	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22542728	11_UHF-0-7-4/002_-E	Single

Suitable cables	
Cable group	U29 - 7 mm / 50 Ohm
Suitable cables	RG_213_/U
	GX_07272

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3356 / Date of publication: 12.07.2025 / uncontrolled copy