

SENCITY® Rail Excel Antenna

1324.17.0089

Properties

- Railway rooftop directional antenna for Wi-Fi bands between 2400 and 2650 MHz
- Vertically polarized radiation pattern
- Rugged design, meets EN 50155 Railway Standard
- Fire retardant according to EN 45545-2 and NFPA-130
- Works also on non-metallic surfaces

**Electrical data**

	Band 1	Band 2	Band 3	Band 4
Frequency	2400 MHz ... 2550 MHz	2550 MHz ... 2590 MHz	2590 MHz ... 2630 MHz	2630 MHz ... 2650 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.5	1.5	1.5	1.5
Gain	14.5 dBi	13.5 dBi	12.5 dBi	11.5 dBi
HPBW vertical	22 °	21 °	21 °	21 °
HPBW horizontal	40 °	33 °	32 °	31 °
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	350 W	350 W	350 W	350 W

Electrical remarks

Remarks	Indicated VSWR values are also valid for installations on non-metallic surfaces (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.
---------	--

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

SENCITY® Rail Excel Antenna

1324.17.0089

Connections	
	Port 1
Band 1	✓
Band 2	✓
Band 3	✓
Band 4	✓

Mechanical data	
Weight	2.2 kg
Dimensions	85 mm x 100 mm x 510 mm (Height x Width x Depth)
Windload	Wind Speed survival: 500 km/h
Remarks	High-voltage-protection: no voltage on RF port, if the catenary line touches the antenna (EN 50124-1, 27.5 kVAC/1min). High-current-protection: Designed acc. to UIC 533, DC-grounded antenna element protection against lightning and short circuit with catenary lines (EN50388, EN 50122-1, 40kA/0.1sec) Corrosion: Low corrosion design according to MIL-F-14072(E), 96 hours Salt Spray test. Mounting: Shall be installed in longitudinal position to the wind/driving direction. Suitable for installation on high-speed trains with a maximum speed of 500 km/hr.

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminum
Back plate/base plate colour	RAL 7043 (dark grey)

Environmental data	
Operation temperature	-55 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-55 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	IP67, IP69
Flammability rating	EN 45545-2 R24 HL3
Solar radiation	UL 746C, F1

Environmental remarks	
Environmental tests: EN 50155:2018-05 Flammability rating: EN45545-2:2013 + A1:2015, NFPA-130:2017 Tested according to ISO 4589-2:2017, NFX 70-100-1:2006, ISO 5659-2:2011. Antennas with production date prior to 01-Oct-2020 do not have NFPA-130 compliance.	

Additional Information	
This product meets the Deutsche Bahn specifications for rolling stock equipment. There is no applicable EU directive nor related harmonized standard for passive antennas. Consequently, there is no CE marking on these antennas and no EU Declaration of Conformity can be issued.	

SENCITY® Rail Excel Antenna
1324.17.0089

Ordering information		
Item description	Item number	Product name
1324.17.0089	84035488	SENCITY® Rail Excel Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3309 / Date of publication: 12.08.2025 / uncontrolled copy