


COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_MMCX-50-0-4/111_O

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Gender	Standard
MMCX	jack	HUBER+SUHNER-MMCX

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0003 kg
Mating cycles	500
Chassis torque	0.4 N
Flange type	round flange / dia. 5
Tab style	Standard

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min		6 N
Interface force max	15 N	15 N

COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_MMCX-50-0-4/111_O

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22660282	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22660282	22_MMCX-50-0-4/111_OH	Bulk 100 pcs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2798 / Date of publication: 12.07.2025 / uncontrolled copy