

COAXIAL CONNECTOR, NEX10, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_NEX10-50-0-3/033_-

Properties

- PIM Stable Interface
- Compact and space saving
- Operating frequency up to 20 GHz
- Excellent return loss and electrical performance
- Interface safe from installation errors



Product configuration		
Interface type	Gender	Standard
NEX10	jack	NEX10

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	20 GHz

Environmental data	
Operation temperature	-55 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85094630	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering Information Table		
Item number	Item description	Packaging type
85094630	23_NEX10-50-0-3/033_-Y	Tray

**COAXIAL CONNECTOR, NEX10, 50 Ohm, Straight panel receptacle, jack (female),
flange mount**

23_NEX10-50-0-3/033_-

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2727 / Date of publication: 12.07.2025 / uncontrolled copy