


COAXIAL CONNECTOR, N, 75 Ohm, Straight bulkhead cable jack (female)

24_N-75-4-2/133_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration	
Gender	Standard
jack	IEC 60169-16_MIL-STD-348A/304_CEECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	75 Ω
Interface frequency	1.5 GHz

Mechanical data	
Weight	0.0393 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	clamped

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, N, 75 Ohm, Straight bulkhead cable jack (female)

24_N-75-4-2/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543628	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543628	24_N-75-4-2/133_NE	Single

Suitable cables	
Cable group	X16 - 4 mm / 75 Ohm --- obsolete (integrated in U18) U16 - 4 mm / 75 Ohm
Suitable cables	RG_59_B/U GX_04273 G_04273-12
Additional cables	GX_04273-12

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2604 / Date of publication: 11.07.2025 / uncontrolled copy