

**COAXIAL ADAPTER, BNC, 50 Ohm, jack / jack (female / female)**

31\_BNC-50-0-1/133\_N

**Properties**

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



| Product configuration |               |                                         |
|-----------------------|---------------|-----------------------------------------|
| Interface type        | Gender        | Standard                                |
| BNC                   | jack (female) | IEC 60169-8_MIL-STD-348A/301_CECC 22120 |
| BNC                   | jack (female) | IEC 61169-8_MIL-STD-348A/301_CECC 22120 |

| Interface and material data |                        |                                   |
|-----------------------------|------------------------|-----------------------------------|
| BNC                         |                        |                                   |
| <b>Piece parts</b>          | <b>Material</b>        | <b>Plating</b>                    |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer conductor             | Brass                  | SUCOPLATE (R) Plating             |
| Body                        | Brass                  | SUCOPLATE (R) Plating             |
| Insulator                   | PFA / PTFE             |                                   |
| BNC                         |                        |                                   |
| <b>Piece parts</b>          | <b>Material</b>        | <b>Plating</b>                    |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer conductor             | Brass                  | SUCOPLATE (R) Plating             |
| Body                        | Brass                  | SUCOPLATE (R) Plating             |
| Insulator                   | PFA / PTFE             |                                   |

| Electrical data     |                                        |
|---------------------|----------------------------------------|
| Impedance           | 50 $\Omega$                            |
| Interface frequency | 4 GHz                                  |
| VSWR                | DC - 4 GHz ( $\leq 1.06 + 0.04 f$ GHz) |

| Mechanical data |           |
|-----------------|-----------|
| Weight          | 0.0123 kg |
| Mating cycles   | 500       |

**COAXIAL ADAPTER, BNC, 50 Ohm, jack / jack (female / female)**

31\_BNC-50-0-1/133\_N

**Environmental data**

|                       |                   |
|-----------------------|-------------------|
| Operation temperature | -65 °C ... 165 °C |
|-----------------------|-------------------|

**Material compliance**

| Item number | Directive / Regulation            | Rating                          | Exemptions / Details |
|-------------|-----------------------------------|---------------------------------|----------------------|
| 22540540    | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|             | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |

**Ordering Information Table**

| Item number | Item description     | Packaging type |
|-------------|----------------------|----------------|
| 22540540    | 31_BNC-50-0-1/133_NE | Single         |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P2419 / Date of publication: 12.07.2025 / uncontrolled copy