

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)
32_MMBX-50-0-1/111_N_-1

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection



Product configuration		
Interface type	Gender	Standard
MMBX	plug (male)	
MMBX	plug (male)	

Interface and material data		
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0001 kg
Mating cycles	100

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)
32_MMBX-50-0-1/111_N_-1**Environmental data**

Operation temperature	-55 °C ... 155 °C
-----------------------	-------------------

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2325 / Date of publication: 12.07.2025 / uncontrolled copy