

**COAXIAL ADAPTER, BMA - SMA, 50 Ohm, plug / jack (male / female)**

33\_BMA-SMA-50-1/199\_U

**Properties**

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



| Product configuration |               |                                          |
|-----------------------|---------------|------------------------------------------|
| Interface type        | Gender        | Standard                                 |
| BMA                   | plug (male)   | IEC 60169-33_MIL-STD-348A/321            |
| SMA                   | jack (female) | IEC 60169-15_MIL-STD-348A/310_CEEC 22110 |

| Interface and material data |                        |                                            |
|-----------------------------|------------------------|--------------------------------------------|
| BMA                         |                        |                                            |
| <b>Piece parts</b>          | <b>Material</b>        | <b>Plating</b>                             |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (without Nickel underplating) |
| Outer conductor             | Stainless steel        |                                            |
| Body                        | Stainless steel        |                                            |
| Insulator                   | PFA / PTFE             |                                            |
| SMA                         |                        |                                            |
| <b>Piece parts</b>          | <b>Material</b>        | <b>Plating</b>                             |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (without Nickel underplating) |
| Outer conductor             | Stainless steel        |                                            |
| Body                        | Stainless steel        |                                            |
| Insulator                   | PFA / PTFE             |                                            |

| Electrical data     |                                                   |
|---------------------|---------------------------------------------------|
| Impedance           | 50 Ω                                              |
| Interface frequency | 18 GHz                                            |
| VSWR                | DC - 18 GHz ( $\leq 1.06 + 0.009 f \text{ GHz}$ ) |

| Mechanical data |           |
|-----------------|-----------|
| Weight          | 0.0021 kg |
| Mating cycles   | 500       |

**COAXIAL ADAPTER, BMA - SMA, 50 Ohm, plug / jack (male / female)**

33\_BMA-SMA-50-1/199\_U

**Environmental data**

|                       |                   |
|-----------------------|-------------------|
| Operation temperature | -65 °C ... 125 °C |
|-----------------------|-------------------|

**Material compliance**

| Item number | Directive / Regulation            | Rating                          | Exemptions / Details |
|-------------|-----------------------------------|---------------------------------|----------------------|
| 22645644    | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|             | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |

**Ordering Information Table**

| Item number | Item description       | Packaging type |
|-------------|------------------------|----------------|
| 22645644    | 33_BMA-SMA-50-1/199_UE | Single         |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2254 / Date of publication: 12.07.2025 / uncontrolled copy