

PROTECTIV CAP, N, jack (female)

62_N-0-0-14

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL

Environmental data

Operation temperature	165°C
-----------------------	-------

Ordering Information Table

Item number	Item description
22660066	62_N-0-0-14/--3_-E

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1800 / Date of publication: 08.10.2023 / uncontrolled copy