


COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle PCB plug (male)

84_MMCX-50-0-1/111_O

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available

**Product configuration**

Interface type	Gender	Standard
MMCX	plug	HUBER+SUHNER-MMCX

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data

Weight	0.0005 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	3.8 mm
Height of stand off HS	0 mm

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min		6 N
Interface force max	15 N	15 N

COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle PCB plug (male)

84_MMCX-50-0-1/111_O

Environmental data			
Operation temperature		-55 °C ... 155 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22658819	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22658819	84_MMCX-50-0-1/111_OH		Bulk 100 pcs
Additional Information			
Remarks		PCB connector without stand-offs	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1294 / Date of publication: 12.07.2025 / uncontrolled copy