

Multicoax breakout, 2x8, MXP (female) to PC24 (female), 50 Ohm, 50 GHz, 152mm
85023135

Properties

- Operating range at up to 50 GHz
- Standard absolute phase matching down to ± 2 ps
- Slide-on mounting – no threading
- Highly flexible and ultra stable Multiflex cable
- Extensive technical support
- 4 mm (0.157 inch) pitch centre-to-centre



Product configuration	
MULTICOAX assembly type	Breakout
Type of cable	MULTIFLEX_53-02
Type description connector A	2x8_21_MXP
Type description connector B	21_PC24
Length	152 mm
Length	6 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	50 GHz

Environmental data	
Operation temperature	-55 °C ... 85 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85023135	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Multicoax breakout, 2x8, MXP (female) to PC24 (female), 50 Ohm, 50 GHz, 152mm
85023135

Ordering information	
Item number	Item description
85023135	MF53/2x8A_21MXP/21PC24_erg/152

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31274 / Date of publication: 23.05.2025 / uncontrolled copy