

Multicoax breakout, 1x8, MXP (female) to PC24 (male), 50 Ohm, 50 GHz, 305mm
85025935

Properties

- Operating range at up to 50 GHz
- Standard absolute phase matching down to ± 2 ps
- Slide-on mounting – no threading
- Highly flexible and ultra stable Multiflex cable
- Extensive technical support
- 4 mm (0.157 inch) pitch centre-to-centre



Product configuration	
MULTICOAX assembly type	Breakout
Type of cable	MULTIFLEX_53-02
Type description connector A	1x8_21_MXP
Type description connector B	11_PC24
Length	305 mm
Length	12 inch
Length type	REF to REF
Electrical data	
Impedance	50 Ω
Max. operating frequency	50 GHz
Environmental data	
Operation temperature	-55 °C ... 85 °C
Ordering information	
Item number	Item description
85025935	MF53/1x8A_21MXP/11PC24/305

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P45751 / Date of publication: 09.09.2024 / uncontrolled copy