

Control Cable AISG 0.5m

86010054

Properties

Connecting cable for
RET (remote electrical tilt)
systems



Mechanical data

Weight	0.15 kg
Dimensions	7.2 mm (Diameter)
Remarks	The male and female connectors are compatible components which are designed to operate under the environmental conditions as described in ETS 300 019-1-4 class 4.1 E.

Environmental data

Operation temperature	-40 °C ... 80 °C
Ingress protection (IP Rating)	Mated / IP 67
Flammability rating	UL 1581-1061 UL 1685 CM IEC 60332-3-24

Additional Information

Connectors: ACS C091 over molded f/m connector IEC 601309
 Mating torque: 0.5 – 1 Nm (The connector should be tightened by hand)
 Signal: 2xAWG24 (twisted pair 100 Ω/1 MHz)
 Power: 3x AWG18 (4A)
 Bending Radius: 45mm

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
 DOCUMENT PIM-P1242 / Date of publication: 05.06.2024 / uncontrolled copy