

Sencity Rail antenna adapter plate

9091.99.0252

Properties

- Compatible with antennas 1399.99.0120, 1399.17.0122, 1399.99.0026 and 1399.17.0094 only
- Made from machined alumium and includes integrated sealing gaskets



Mechanical data	
Weight	1.6 kg
Dimensions	25 mm x 100 mm x 260 mm (Height x Width x Depth)
Windload	Wind Speed survival: 500 km/h

Environmental data	
Operation temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP69
Flammability rating	EN 45545-2

Environmental remarks	
IP Rating IP 69 (interface from roof to adapter plate, from adapter plate to antenna see datasheet of antenna)	
The adaptor plate has been tested in combination with the Sencity Rail antenna and together met the following requirements: EN50155 High voltage protection EN 50124-1 High current protection (EN50388,EN50122-1,40kA/0.1sec)	

Additional Information	
This product is not compatible to all Sencity Rail antennas. Please check the datasheet of the antenna.	

Ordering information	
Item number	Item description
84148131	9091.99.0252

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1187 / Date of publication: 11.11.2024 / uncontrolled copy